


Bürstenloser Gleichstrommotor (BLDC)

RB-8530-C8

Anwendungen: Sauerstoffkonzentratoren mit hohem Durchfluss, Medizintechnik und Serviceroboter



MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY						STALL	
	OPERATING RANGE	NOMINAL	SPEED rpm	CURRENT A	SPEED rpm	CURRENT A	TORQUE g.cm	TORQUE mN-m	OUTPUT W	EFF %	TORQUE g.cm	TORQUE mN-m
RB-8530-C8-N-01	12.0-26.0V	12.0V CONSTANT	2300	2.8	1850	21	10200	1000	205	79	89800	8810
RB-8530-C8-N-02	12.0-26.0V	24.0V CONSTANT	2400	1.5	1900	11	10200	1000	210	80	115770	11350
RB-8530-C8-N-03	24.0V-40.0V	36.0V CONSTANT	2300	1	1850	7	10200	1000	210	80	115770	11350
RB-8530-C8-N-04	6.0V-26.0V	18.0V CONSTANT	2300	3.1	1850	14	10200	1000	205	76.84	89800	8810

Wellenüberstand, Leistungsdaten und EMV-Maßnahmen kundenspezifisch. Details auf Anfrage.

